



GAR2026TN, Mech Ground Conn, Cable to Rod/Pipe, Tin Plated

By Burndy

Catalog # [GAR2026TN](#)

Mechanical Grounding Connector, Cable to Rod or Pipe, 4 AWG (Sol)-2/0 AWG (Str), 3" Pipe, 3"-3-1/2" Rod, Tin Plated.



Features

- Parallel or 90° Copper Cable Connection
- One-wrench installation
- Rated for Direct Burial in earth or concrete

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified Industry Standard(s)	Contact Manufacturer UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Pipe or Round Tube Size	3 in
Conductor - Copper Solid Size	• 4 • 3 • 2 • 1 • 1/0 • 2/0 • 3/0
Conductor - Copper Solid Size Range	4 AWG-2/0 AWG
Conductor - Rod Size Range	3
Conductor Type	• CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size
Conductor - Copper Str Size Range	5 AWG - 2/0 AWG
Conductor - Copper Str Size	• 5 • 4 • 3 • 2 • 1 • 1/0

Conductor - Rod Size	• 2/0
Conductor - Copper Tube Std Size Range	3 - 3.5 in
Conductor - Copper Tube Std Size	3-3 1/2
	• 3 • 3 1/2

Dimensions

Package Height	0.000 in
Dimension - Height mm	142.7 mm
Dimension - Height inch	5.62 in
Package Weight	0.000 lb.
Dimension - Width mm	122 mm
Dimension - Width inch	4.81 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	40 mm
Dimension - B Length inch	3.50 in
Dimension - Outside Diameter inch	3.50 in
Dimension - Length Overall inch	1.56 in

Force Related

Installation Torque Recommended in-lb	240 LBS/in
---------------------------------------	------------

General

Plated	Y
Material - Hardware	DURIUM™ Silicon Bronze
UPC	621945133846
U Bolt Type	267
Material	Copper Alloy
Plating Type	Tin - Electro Plated
UPC 12 Digit	621945133846
UPC 14 Digit GTIN	00621945133846

Logistics

Minimum Pack Quantity	1
Pallet Quantity	975
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)

