



GAR2129W, Mech Ground Conn, Cable to Rod or Pipe, Tin Plated

By Burndy
Catalog # [GAR2129W](#)



Mechanical Grounding Connector, Cable to Rod or Pipe, 2/0 AWG (Sol) -250 kcmil, 3-1/2" Pipe, 3-1/2"-4" Rod, Tin Hot Dipped

Features

- Parallel or 90° Copper Cable Connection
- One-wrench installation
- Rated for Direct Burial in earth or concrete

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Pipe or Round Tube Size	3 1/2 in
Conductor - Copper Solid Size	• 2/0 • 3/0 • 4/0
Conductor - Copper Solid Size Range	2/0 AWG- 250 Kcmil
Conductor Type	• CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size
Conductor - Copper Str Size Range	1/0 AWG - 250 kcmil
Conductor - Copper Str Size	• 1/0 • 2/0 • 3/0 • 4/0 • 250
Conductor - Rod Size	3.5 - 4.0 in
Conductor - Copper Tube Std Size Range	3 1/2-4

Conductor - Copper Tube Std Size	• 3 1/2 • 4
----------------------------------	---

Dimensions

Package Height	0.000 in
Dimension - Height mm	158.8 mm
Dimension - Height inch	6.25 in
Package Weight	0.000 lb.
Dimension - Width mm	135 mm
Dimension - Width inch	5.31 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	46 mm
Dimension - B Length inch	4.00 in
Dimension - Outside Diameter inch	4.00 in
Dimension - Length Overall inch	1.81 in

Force Related

Installation Torque Recommended in-lb	240 LBS/in
---------------------------------------	------------

General

Plated	Y
Material - Hardware UPC	DURIUM™ Silicon Bronze 781810117040
U Bolt Type	264
Material	Copper Alloy
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810117040
UPC 14 Digit GTIN	00781810117040

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)