



GAR2134, Mech Ground Conn, Cable to Rod or Pipe

By Burndy
Catalog # [GAR2134](#)



Mechanical Grounding Connector, Cable to Rod or Pipe, 300 kcmil -500 kcmil, 3-1/2" Pipe, 3-1/2"-4" Rod

Features

- Parallel or 90° Copper Cable Connection
- One-wrench installation
- Rated for Direct Burial in earth or concrete

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Pipe or Round Tube Size	3 1/2 in
Conductor - Copper Str Size	• 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil
Conductor - Rod Size	3.5 - 4.0 in
Conductor - Copper Solid Size Range	300 Kcmil -500 Kcmil
Conductor Type	• CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size
Conductor - Copper Str Size Range	300 kcmil - 500 kcmil
Conductor - Copper Tube Std Size Range	3 1/2 IPS IPS
Conductor - Copper Tube Std Size	3 1/2 IPS IPS

Dimensions

Package Height	0.000 in
Dimension - Height mm	171.5 mm
Dimension - Height inch	6.75 in
Dimension - Height fraction	6-3/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	60 mm
Dimension - Outside Diameter inch	4.00 in
Dimension - Width fraction	5-3/4 in
Dimension - Width mm	145 mm
Dimension - Width inch	5.69 in
Dimension - B Length inch	4.25 in
Dimension - Length Overall inch	2.38 in

Force Related

Installation Torque	480 LBS/in
Recommended in-lb	

General

Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
UPC	781810237052
U Bolt Type	436
Material	Copper Alloy
Plating Type	Bright Dipped
UPC 12 Digit	781810237052
UPC 14 Digit GTIN	00781810237052

Logistics

Minimum Pack Quantity	4
Pallet Quantity	288
Carton Quantity	8

Product Assets

[Catalog \[English\]](#)