



GAR214C, Mech Ground Conn, Cable to Rod or Pipe

By Burndy

Catalog # [GAR214C](#)

Mechanical Grounding Connector, Cable to Rod or Pipe, 8 AWG
-4 AWG, 3-1/2" Pipe, 3-1/2"-4" Rod



Features

- Parallel or 90° Copper Cable Connection
- One-wrench installation
- Rated for Direct Burial in earth or concrete

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Pipe or Round Tube Size	3 1/2 in
Conductor - Copper Str Size	• 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG
Conductor - Rod Size	3.5 - 4.0 in
Conductor - Copper Solid Size	• 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG
Conductor - Copper Solid Size Range	8 AWG-4 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size
Conductor - Copper Str Size Range	9 AWG - 4 AWG
Conductor - Copper Tube Std Size Range	3 1/2 IPS IPS

Conductor - Copper Tube Std Size3 1/2 IPS IPS

Dimensions

Package Height	0.000 in
Dimension - Height mm	158.8 mm
Dimension - Height inch	6.25 in
Dimension - Height fraction	6-1/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	33 mm
Dimension - Outside Diameter inch	4.00 in
Dimension - Width fraction	5-3/8 in
Dimension - Width mm	135 mm
Dimension - Width inch	5.31 in
Dimension - B Length inch	4.00 in
Dimension - Length Overall inch	1.31 in

Force Related

Installation Torque Recommended in-lb	240 LBS/in
---------------------------------------	------------

General

Material - Hardware Plated	DURIUM™ Silicon Bronze N
UPC	781810237151
U Bolt Type	264
Material	Copper Alloy
Plating Type	Bright Dipped
UPC 12 Digit	781810237151
UPC 14 Digit GTIN	00781810237151

Logistics

Minimum Pack Quantity	6
Pallet Quantity	900
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)

