



GAR2226TN, Mech Ground Conn, Cable to Rod/Pipe, Tin Plated

By Burndy
Catalog # [GAR2226TN](#)



To Rod or Pipe with the Same Connector.

Features

- Parallel or 90° Copper Cable Connection
- One-wrench installation
- Rated for Direct Burial in earth or concrete

Specifications

Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	EX
Status	
Certification - UL Listed Direct	Yes
Burial	
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Type	• CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size
----------------	---

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Plated	N
UPC	621945456839
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	621945456839
UPC 14 Digit GTIN	00621945456839

Logistics

Minimum Pack Quantity	1
Pallet Quantity	540
Carton Quantity	2

Product Assets

[Catalog \[English\]](#)