



GAR2226W, Mech Ground Conn, Cable to Rod or Pipe, Tin Plated

By Burndy

Catalog # [GAR2226W](#)

Mechanical Grounding Connector, Cable to Rod or Pipe, 4 AWG (Sol)-2/0 AWG (Str), 4" Pipe, 4"-4-1/2" Rod, Tin Hot Dipped.



Features

- Parallel or 90° Copper Cable Connection
- One-wrench installation
- Rated for Direct Burial in earth or concrete

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Pipe or Round Tube Size	4 in
Conductor - Copper Solid Size	• 4 • 3 • 2 • 1 • 1/0 • 2/0 • 3/0
Conductor - Copper Solid Size Range	4 AWG-2/0 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size
Conductor - Copper Str Size Range	5 AWG - 2/0 AWG
Conductor - Copper Str Size	• 5 • 4 • 3 • 2 • 1 • 1/0 • 2/0

Conductor - Rod Size	4.0 - 4.5 in
Conductor - Copper Tube Std Size Range	4-4 1/2
Conductor - Copper Tube Std Size	• 4 • 4 1/2

Dimensions

Package Height	0.000 in
Dimension - Height mm	162.1 mm
Dimension - Height inch	6.38 in
Package Weight	0.000 lb.
Dimension - Width mm	148 mm
Dimension - Width inch	5.81 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	40 mm
Dimension - B Length inch	4.50 in
Dimension - Outside Diameter inch	4.50 in
Dimension - Width fraction	5-7/8 in
Dimension - Length Overall inch	1.56 in

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	

General

Plated	Y
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810117217
U Bolt Type	261
Material	Copper Alloy
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810117217
UPC 14 Digit GTIN	00781810117217

Logistics

Minimum Pack Quantity	1
Pallet Quantity	640
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)

