



GAR2229TN, Mechanical Grounding Connector, Cable to Rod or Pipe, Tin Plated

By Burndy
Catalog # [GAR2229TN](#)

Mechanical Grounding Connector, Cable to Rod or Pipe, 2/0 AWG (Sol) -250 kcmil, 4" Pipe, 4"-4-1/2" Rod, Tin Plated.

Features

- Parallel or 90° Copper Cable Connection
- One-wrench installation
- Rated for Direct Burial in earth or concrete

Specifications

Standards - RoHS Compliance Status	EX
Certification - CSA Approved	No
UL Listed	Yes
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor - Copper Solid Size	• 2/0 • 3/0 • 4/0
Conductor - Copper Solid Size Range	2/0 AWG-250 Kcmil
Conductor - Pipe or Round Tube Size	4 in
Conductor - Rod Size	4.0 - 4.5 in
Conductor - Copper Str Size	• 1/0 • 2/0 • 3/0 • 4/0 • 250
Conductor - Copper Str Size Range	1/0 AWG - 250 kcmil
Conductor - Copper Tube Std Size	• 4 • 4 1/2



Conductor - Copper Tube Std Size Range 4-4 1/2

Dimensions

Dimension - Width inch	5.82 in
Dimension - Width mm	148 mm
Dimension - B Length inch	4.50 in
Dimension - Outside Diameter inch	4.50 in
Dimension - L Length Overall mm	46 mm
Dimension - Height inch	6.38 in
Dimension - Height mm	162.1 mm
Dimension - Length Overall inch	1.81 in

Force Related

Installation Torque Recommended in-lb	240 LBS/in
---------------------------------------	------------

General

U Bolt Type	261
Plating Type	Tin - Hot Dipped
UPC	621945449398

Logistics

Minimum Pack Quantity	1
Carton Quantity	6
Pallet Quantity	756

Product Assets

[Catalog \[English\]](#)



A Hubbell brand