



GAR2234, Mech Grounding Connector, Cable to Rod or Pipe

By Burndy

Catalog # [GAR2234](#)

Mechanical Grounding Connector, Cable to Rod or Pipe, 300 - 500 kcmil,
4" to 4-1/2" Rod, 4" Pipe, Bright Dipped



Features

- Parallel or 90° Copper Cable Connection
- One-wrench installation
- Rated for Direct Burial in earth or concrete

Application

For Joining A Range Of Cable, Parallel Or At Right Angles To Rod Or Tube, Direct Burial Cable, Fence Post

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	EX
Status	
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Pipe or Round Tube Size	4 in
Conductor - Copper Str Size	• 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil
Conductor - Rod Size	4.0 - 4.5 in
Conductor - Copper Solid Size Range	300 Kcmil -500 Kcmil
Conductor Type	• CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size
Conductor - Copper Str Size Range	300 kcmil - 500 kcmil
Conductor - Copper Tube Std Size Range	4 IPS IPS
Conductor - Copper Tube Std Size	4 IPS IPS

Dimensions



A Hubbell brand

Package Height	0.000 in
Dimension - Height mm	174.8 mm
Dimension - Height inch	6.88 in
Dimension - Height fraction	6-7/8 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	60 mm
Dimension - Outside Diameter inch	4.50 in
Dimension - Width fraction	6-1/4 in
Dimension - Width mm	157 mm
Dimension - Width inch	6.19 in
Dimension - B Length inch	5.00 in
Dimension - Length Overall inch	2.38 in

Force Related

Installation Torque Recommended in-lb	480 LBS/in
---------------------------------------	------------

General

Product Family	Grounding and Bonding Connectors>Copper Mechanical Grounding Connectors>Cable(s) to Ground Rod/Pipe/Tube (GAR/GD/GK)>Single Conductor(GAR)
Material - Hardware Plated	DURIUM™ Silicon Bronze No
Sub Brand	MECHANICAL CONNECTOR
Product Type	Mechanical
UPC	781810237809
Type	GAR
U Bolt Type	416
Material	Copper Alloy
Plating Type	Bright Dipped
UPC 12 Digit	781810237809
UPC 14 Digit GTIN	00781810237809

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)