



GAR2426W-WEEB, Mech Ground Conn, Cable to Rod/Pipe

By Burndy
Catalog # [GAR2426W-WEEB](#)

Mechanical grounding connector, Cable to Rod or Pipe, 4 AWG
Sol-2/0 AWG Str, 5" Pipe, Tin Plated, WEEB Washer



Features

- UL467 Listed
- Acceptable for Direct Burial
- Tin-Plated Copper Connector and Hardware
- WEEB Washer penetrates various non-conductive coatings
- Installation Torque: 240 in-lb

Specifications

Buy America(n) Qualified	Contact Manufacturer
UL Listed	Yes

Conductor

Conductor - Pipe or Round Tube Size	4" Pipe, 4" to 4-1/2" Rod
Conductor - Copper Solid Size	#4 AWG - 2/0 AWG
Conductor - Copper Str Size	#4 AWG - 2/0 AWG
Conductor - Rod Size	4" to 4-1/2" Rod

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

UPC	621945702882
U Bolt Type	DURIUM™ Silicon Bronze
Material	Tin-plated Copper Alloy, DURIUM™ Silicon Bronze Hardware, Stainless Steel WEEB Washer
Finish Type	Tin Plated

Product Assets

[Catalog \[English\]](#)