



GAR244C, Mech Grounding Connector, Cable to Rod or Pipe

By Burndy

Catalog # [GAR244C](#)

Mechanical Grounding Connector, Cable to Rod or Pipe, 8 AWG (Sol) - 4 AWG (STR), 5" Pipe, Bright Dipped.



Features

- Parallel or 90° Copper Cable Connection
- One-wrench installation
- Rated for Direct Burial in earth or concrete

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Pipe or Round Tube Size	5 in
Conductor - Copper Solid Size	• 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG
Conductor - Copper Solid Size Range	8 AWG-4 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size
Conductor - Copper Str Size Range	9 AWG - 4 AWG
Conductor - Copper Str Size	• 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG
Conductor - Copper Tube Std Size Range	5 IPS IPS

Conductor - Copper Tube Std Size5 IPS IPS

Dimensions

Package Height	0.000 in
Dimension - Height mm	196.9 mm
Dimension - Height inch	7.75 in
Dimension - Height fraction	7-3/4 in
Package Weight	0.000 lb.
Dimension - Width mm	175 mm
Dimension - Width inch	6.88 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	40 mm
Dimension - B Length inch	4.50 in
Dimension - Outside Diameter inch	5.56 in
Dimension - Width fraction	6-7/8 in
Dimension - Length Overall inch	1.56 in

Force Related

Installation Torque Recommended in-lb	240 LBS/in
---------------------------------------	------------

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810001479
U Bolt Type	122
Material	Copper Alloy
Plating Type	Bright Dipped
UPC 12 Digit	781810001479
UPC 14 Digit GTIN	00781810001479

Logistics

Minimum Pack Quantity	4
Pallet Quantity	360
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)

