



GAR3904BUW, Mech Ground Conn, Cond to Water Pipe, Tin Plated

By Burndy
Catalog # [GAR3903BUW](#)

Mechanical Grounding Connector - Conductor to Water Pipe, #4-4/O AWG, 1-1/4" to 2" Pipe, 3/8" Stud, Tin Plated



Features

- Cable clamp swivels at 90°
- One-wrench installation for simplified installation
- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets

Specifications

Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Pipe or Round Tube Size	1.25 - 2 in
Conductor - Copper Solid Size Range	4 AWG - 4/O AWG

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Force Related

Installation Torque Recommended in-lb	200 LBS/in
---------------------------------------	------------

General

Plated	N
Material - Hardware	Copper Alloy
UPC	781810569894
Material	Bronze, Silicon (DURIUM is a trademark)
Plating Type	Unplated
UPC 12 Digit	781810569894
UPC 14 Digit GTIN	00781810569894

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)