



GAR3905TN, Mech Ground Conn, Cable to Rod/Pipe, Tin Plated

By Burndy
Catalog # [GAR3905TN](#)

Mechanical Grounding Connector, Cable to Rod or Pipe, #4-4/0 Str AWG Cu, 4-5" IPS

Features

- Cable clamp swivels at 90°, permits parallel grounding of one pipe on a 90° cable run for grounding several parallel pipes
- One-wrench installation for simplified installation
- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- Provides quality assurance to recognized industry NEC standards from an independent part

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Pipe or Round Tube Size	4 - 5 in
-------------------------------------	----------



Conductor - Copper Solid Size Range	4 AWG - 4/0 AWG
-------------------------------------	-----------------

Force Related

Installation Torque Recommended in-lb	200 LBS/in
---------------------------------------	------------

General

Plated	N
UPC	781810526798
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810526798
UPC 14 Digit GTIN	00781810526798

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)