



GAR3906BUTN, Mechanical Grounding Connector, Tin Plated

By Burndy
Catalog # [GAR3906BUTN](#)



ACTUAL O.D.: 6.62 in. [168] 4 Str (.232) - 4/0 Str (.528) AWG
25mm2 Str [6.6] - 95mm2 str [12.0] TQ: 200 lb-in [22.5 Nm] Tin
Plated

Features

- Cable clamp swivels at 90°
- One-wrench installation for simplified installation
- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Pipe or Round Tube Size	6 in
Conductor - Copper Solid Size Range	4 AWG - 4/0 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	215.9 mm
Dimension - Height inch	8.50 in

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Outside Diameter inch	6.62 in
Dimension - Length Overall inch	1.75 in

Force Related

Installation Torque Recommended in-lb	200 lb-in
---------------------------------------	-----------

General

Plated	N
UPC	781810501115
Material	Copper Alloy
Plating Type	Tin Electro Plated
UPC 12 Digit	781810501115
UPC 14 Digit GTIN	00781810501115

Logistics

Minimum Pack Quantity	12
Pallet Quantity	546
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)