



GAR3907TC, Mech Ground Conn, For 2 Hole Lug to Pipe or Rod

By Burndy
Catalog # [GAR3907TC](#)



Accommodates 8" IPS, 8.62" OD, 3/8" Hardware, 2-Hole Lug pad 3/8" Bolts on 1" Centers (ordered separately)

Features

- Large, smooth connector contact area between pipe and ground clamp to maximize contact area between connector and pipe
- Pre-drilled pad for 2-3/8" bolts on 1" centers to allow for direct mounting of 2-hole compression terminals up to 750 kcmil to pipe
- One-wrench installation
- UL467 Listed for the US and Canadian Markets

Application

For Direct Burial, Water Pipe As Well As Structural And Reinforcing Rod Shapes

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Pipe or Round Tube Size	8 in
Conductor - Copper Tube EH Size	8

Configuration

Physical Attribute - Pad Configuration	3.63 x 2.67 - 3 Holes
Physical Attribute - Number of Holes	3

Dimensions

Package Height	0.000 in
Dimension - Height mm	254 mm

Dimension - Height inch	10.00 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Outside Diameter inch	8.62 in
Dimension - Thread Size	3/8-16
Dimension - Threads per inch	16
Dimension - Bolt Size fraction	3/8
Dimension - Width mm	286 mm
Dimension - Width inch	11.25 in
Dimension - Length Overall inch	3.63 in

Force Related

Installation Torque Recommended	240 lb-in in-lb
---------------------------------	-----------------

General

Product Family	Grounding and Bonding Connectors>Copper Mechanical Grounding Connectors>Water Pipe Grounding Connectors
Material - Hardware Plated	DURIUM™ Silicon Bronze No
Sub Brand	MECHANICAL CONNECTOR
Product Type	Mechanical
UPC	781810001608
Type	Rod or Tube Clamp with Mounting Pad
U Bolt Type	1028
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810001608
UPC 14 Digit GTIN	00781810001608

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)