



# GAR3909BU, Mech Ground Conn, Conductor to Water Pipe

By Burndy  
Catalog # [GAR3909BU](#)

Mechanical Grounding Connector, Conductor to Water Pipe, 4-4/0 AWG, 12" Pipe, 3/8" Stud, silicon bronze hardware



## Features

- Cable clamp swivels at 90°
- One-wrench installation for simplified installation
- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets

## Specifications

|                                         |                      |
|-----------------------------------------|----------------------|
| Certification - ETL                     | No                   |
| Certification - UL Recognized           | No                   |
| Standards - Industry Standards Met      | UL467                |
| Standards - RoHS Compliance Status      | CM                   |
| Certification - cULus                   | No                   |
| Certification - UL Listed Direct Burial | Yes                  |
| Buy America(n) Qualified                | Contact Manufacturer |
| Industry Standard(s)                    | UL467                |
| UL Listed                               | Yes                  |
| Certification - CSA Approved            | No                   |

## Conductor

|                                        |                                                                                                                                                 |
|----------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - Pipe or Round Tube Size    | 12 in                                                                                                                                           |
| Conductor - Copper Solid Size Range    | 4 AWG - 4/0 AWG                                                                                                                                 |
| Conductor - Copper Str Size Range      | 4 AWG - 4/0 AWG                                                                                                                                 |
| Conductor - Copper Str Size            | <ul style="list-style-type: none"><li>• 4</li><li>• 3</li><li>• 2</li><li>• 1</li><li>• 1/0</li><li>• 2/0</li><li>• 3/0</li><li>• 4/0</li></ul> |
| Conductor - Copper Tube Std Size Range | 12                                                                                                                                              |

Conductor - Copper Tube Std Size 12

## Dimensions

|                                   |           |
|-----------------------------------|-----------|
| Package Height                    | 0.000 in  |
| Dimension - Height mm             | 355.6 mm  |
| Dimension - Height inch           | 14.00 in  |
| Package Weight                    | 0.000 lb. |
| Dimension - Width mm              | 375 mm    |
| Dimension - Width inch            | 14.75 in  |
| Package Length                    | 0.000 in  |
| Package Width                     | 0.000 in  |
| Dimension - B Length inch         | 1.75 in   |
| Dimension - Outside Diameter inch | 12.75 in  |
| Dimension - Length Overall inch   | 1.75 in   |

## Force Related

|                                       |           |
|---------------------------------------|-----------|
| Installation Torque Recommended in-lb | 200 lb-in |
|---------------------------------------|-----------|

## General

|                     |                        |
|---------------------|------------------------|
| Plated              | N                      |
| Material - Hardware | DURIUM™ Silicon Bronze |
| UPC                 | 781810001561           |
| U Bolt Type         | 1030                   |
| Material            | Copper Alloy           |
| Plating Type        | Unplated               |
| UPC 12 Digit        | 781810001561           |
| UPC 14 Digit GTIN   | 00781810001561         |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
| Pallet Quantity       | 1 |
| Carton Quantity       | 4 |

## Product Assets

[Catalog \[English\]](#)



A Hubbell brand