



GAR3909TC, Mech Ground Conn, For 2 Hole Lug to Pipe or Rod

By Burndy
Catalog # [GAR3909TC](#)

Mechanical Ground Connector, For 2 Hole Lug to Water Pipe or Rod, 12" IPS, 3/8" Bolt



Features

- Large, smooth connector contact area between pipe and ground clamp to maximize contact area between connector and pipe
- Pre-drilled pad for 2-3/8" bolts on 1" centers to allow for direct mounting of 2-hole compression terminals up to 750 kcmil to pipe
- One-wrench installation
- UL467 Listed for the US and Canadian Markets

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Pipe or Round Tube Size	12 in
Conductor - Copper Tube EH Size	12

Configuration

Physical Attribute - Pad Configuration	3.63 x 2.67 - 3 Holes
Physical Attribute - Number of Holes	3

Dimensions

Package Height	0.000 in
Dimension - Height mm	355.6 mm
Dimension - Bolt Size fraction	3/8
Dimension - Height inch	14.00 in
Package Weight	0.000 lb.
Dimension - Width mm	387 mm
Dimension - Width inch	15.25 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - Outside Diameter inch	12.75 in
Dimension - Thread Size	3/8-16
Dimension - Threads per inch	16
Dimension - Length Overall inch	3.63 in

Force Related

Installation Torque	240 lb-in
Recommended in-lb	

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810001622
Type	Rod or Tube Clamp with Mounting Pad
U Bolt Type	1030
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810001622
UPC 14 Digit GTIN	00781810001622

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)