



GAR396925BU, Mech Ground Conn, Conductor to Water Pipe

By Burndy
Catalog # [GAR396925BU](#)

Mechanical Grounding Connector - Conductor to Water Pipe, #8
- 1/0 AWG; 2-1/2" Pipe; UL/CSA; Rated for Direct Burial

Features

- Cable clamp swivels at 90°
- One-wrench installation for simplified installation
- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets

Specifications

Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467

Conductor

Conductor - Pipe or Round Tube Size	2.50 in
Conductor - Copper Solid Size Range	#8 AWG - 1/0 AWG
Conductor - Copper Str Size Range	8 AWG - 1/0 AWG
Conductor - Copper Str Size	• 8 • 7 • 6 • 5 • 4 • 3 • 2 • 1 • 1/0
Conductor - Copper Tube Std Size Range	2 1/2



Conductor - Copper Tube Std Size 2 1/2

Dimensions

Package Height	0.000 in
Dimension - Height mm	101.6 mm
Dimension - Height inch	4.00 in
Package Weight	0.000 lb.
Dimension - Width mm	114 mm
Dimension - Width inch	4.50 in
Package Length	0.000 in
Package Width	0.000 in

Force Related

Installation Torque Recommended in-lb	200 lb-in
---------------------------------------	-----------

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810421970
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810421970
UPC 14 Digit GTIN	00781810421970

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)



A Hubbell brand