



GAR6426TN, Mech Ground Conn, Cable to Rod/Pipe, Tin Plate

By Burndy
Catalog # [GAR6426TN](#)

Mechanical Grounding Connector, 4 Sol-2/0 Str, Pipe Size: 3/8" IPS, Rod Size: 5/8"-3/4", Tin Plated



Features

- Wire to Rebar
- Tin-Plated Fence Post Grounding Connector
- Wire to Pipe
- One-wrench installation
- Rated for Direct Burial in earth or concrete
- UL467 Listed for US and Canadian Markets
- Select connectors qualified to IEEE-837-2014

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Pipe or Round Tube Size	3/8 in
Conductor - Copper Solid Size Range	4 AWG-2/0 AWG
Conductor - Rod Size	0.625in - 0.75in

Dimensions

Package Height	0.000 in
----------------	----------

Package Weight	0.000 lb.
Dimension - Width mm	52 mm
Dimension - Width inch	2.06 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	40 mm
Dimension - B Length inch	1.19 in

Force Related

Installation Torque	240 lb-in
Recommended in-lb	

General

Plated	N
UPC	781810544266
Material	Copper Alloy
Plating Type	Tin Plated
UPC 12 Digit	781810544266
UPC 14 Digit GTIN	00781810544266

Logistics

Minimum Pack Quantity	1000
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)