



GB26T4GSTN, Mechanical Grounding Connector, Cable to Bar, Galvanized Steel, Tin Plated

By Burndy
Catalog # [GB26T4GSTN](#)

Mechanical Grounding Connector, Cable to 1/2" Thick Bar, 4 AWG (Sol)-2/0 AWG (Str), Hardware: Galvanized Steel, Tin Plated

Features

- High copper alloy tin-plated ground connector for joining a range of cable to 1/4" thick bar
- Type GB separates cable from bar
- One-wrench installation
- UL467 Listed, suitable for Direct Burial in earth or concrete

Specifications

Certification - CSA Approved No
Certification - UL Listed Direct Burial Yes

Conductor

Conductor - Copper Solid Size Range 4 AWG-2/0 AWG

Dimensions

Dimension - Width inch 1.56 in
Package Length 0.000 in
Package Width 0.000 in
Package Weight 0.000 lb.
Dimension - B Length inch 1.06 in



Dimension - Length Overall inch 0.94 in
Dimension - Height inch 2.18 in
Package Height 0.000 in
Dimension - Height mm 55.4 mm
Dimension - Width fraction 1-5/9 in

Force Related

Installation Torque Recommended in-lb 240 lb-in

General

Plating Type Tin Plated
UPC 621945461635

Logistics

Minimum Pack Quantity 25
Carton Quantity 1
Pallet Quantity 1

Product Assets

[Catalog \[English\]](#)