



GB26TN, Mech Ground Conn, Copper Cable to Bar, Tin Plated

By Burndy
Catalog # [GB26TN](#)



Copper Cable to Bar, Accommodates: 4 AWG Sol-2/0 AWG Str to 1/4" Thick Bar, Tin Plated

Features

- High copper alloy ground connector for joining a range of cable to 1/4" thick bar
- Type GB separates cable from bar
- One-wrench installation
- UL467 Listed
- Suitable for Direct Burial in earth or concrete

- 1/0
- 2/0 AWG

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG
Conductor - Copper Solid Size Range	4 AWG-2/0 AWG
Conductor - Copper Str Size Range	4 AWG-2/0 AWG
Conductor - Copper Str Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	44.2 mm
Dimension - Height inch	1.74 in
Package Weight	0.000 lb.
Dimension - Width inch	1.42 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	24 mm
Dimension - Width fraction	1-3/7 in
Dimension - Length Overall inch	0.94 in

Force Related

Installation Torque	240 lb-in
Recommended in-lb	

General

Physical Attribute - Screw Type	Hexagonal Bolt
Plated	Y
UPC	781810079294
Material Type - Screw	DURIUM™ Silicon Bronze
Material	Copper Alloy
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810079294
UPC 14 Digit GTIN	00781810079294

Logistics

Minimum Pack Quantity	1
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)