



GB29G73, Mechanical Grounding Connector, Cable to Bar

By Burndy
Catalog # [GB29G73](#)

Mechanical Grounding Connector, 2/0 AWG (Sol) -250 kcmil, 1/2" Stud

Features

- Mechanical Grounding Connector
- 2/0 AWG (Sol)-250 kcmil
- 1/2" Stud

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size Range	2/0 AWG - 250 kcmil
-------------------------------------	---------------------

Dimensions

Package Height	0.000 in
Dimension - Height mm	83 mm
Dimension - Height inch	3.25 in
Package Weight	0.000 lb.

Dimension - Width inch	2.03 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	38 mm
Dimension - Width fraction	1-6/7 in
Dimension - Length Overall inch	1.49 in

Force Related

Installation Torque Recommended in-lb	480 lb-in
---------------------------------------	-----------

General

Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
UPC	781810466438
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810466438
UPC 14 Digit GTIN	00781810466438

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1728
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)