



GB44T10W, Mech Ground Conn, Cable to Bar, Tin Plated

By Burndy
Catalog # [GB44T10W](#)

Mechanical Grounding Connector, Cable to 1/4" - 1 1/4" Thick Bar, 800 kcmil - 1000 kcmil, 5/8" Stud, 3-1/6" Width, Hot Tin Dipped

Features

- Mechanical Grounding Connector
- Cable to 1/4"-1-1/4" Thick Bar
- 800-1000 kcmil
- 5/8" Stud
- Hot Tin Dipped

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size Range	800 KCMIL - 1000 KCMIL
Conductor - Copper Str Size Range	800 kcmil - 1000 kcmil
Conductor - Copper Str Size	• 800 kcmil • 850 kcmil • 900 kcmil • 1000 kcmil

Dimensions

Package Height	0.000 in
----------------	----------

Dimension - Height mm	108.7 mm
Dimension - Height inch	4.28 in
Package Weight	0.000 lb.
Dimension - Width inch	3.16 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	45 mm
Dimension - B Length inch	1.75 in
Dimension - Width fraction	3-1/6 in
Dimension - Length Overall inch	1.75 in

Force Related

Installation Torque	660 lb-in
Recommended in-lb	

General

Physical Attribute - Screw Type	Oval Shank Bolt
Plated	Y
UPC	781810116890
Material Type - Screw	DURIUM™ Silicon Bronze
Material	Copper Alloy
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810116890
UPC 14 Digit GTIN	00781810116890

Logistics

Minimum Pack Quantity	2
Pallet Quantity	672
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)