



GBL30STN, Mech Ground Conn, Cable to Bar, Galv Steel, Tin

By Burndy
Catalog # [GBL30GSTN](#)

Cast Copper Alloy Ground Connector, 4 AWG Sol. - 300 kcmil, 1/2" Stud, 1-1/2" Width, Galvanized Steel Hardware, Tin Plated



Features

- Cast Copper Alloy Ground Connector
- 4 AWG (Sol)-300 kcmil
- 1/2" Stud
- Tin Plated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - Copper Solid Size Range	4 AWG - 300 KCMIL
Conductor - Copper Str Size Range	4 AWG - 300 kcmil
Conductor - Copper Str Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil

Dimensions

Package Height	0.000 in
Dimension - Height mm	58.9 mm
Dimension - Height inch	2.32 in
Package Weight	0.000 lb.
Dimension - Width mm	38 mm
Dimension - Width inch	1.50 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	48 mm
Dimension - Hole Size inch	0.56 in
Dimension - Bus Thickness inch	0.32 in
Dimension - Length Overall inch	1.88 in
Dimension - Stud Size inch	33/64

Force Related

Installation Torque	480 lb-in
Recommended in-lb	

General

Physical Attribute - Screw Type	Hexagonal Bolt
Plated	Y
Material - Hardware	Galvanized Steel
UPC	781810246849
Material	Copper Alloy
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810246849
UPC 14 Digit GTIN	00781810246849

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)