



GBL30W, Mech Ground Conn, Cable to Bar, Tin Plated

By Burndy
Catalog # [GBL30W](#)

Cast Copper Alloy Mechanical Ground Connector, Cable to Bar, 4 AWG Sol-300 kcmil, 1/2" Stud

Features

- Cast Copper Alloy Ground Connector
- 4 AWG (Sol)-300 kcmil
- 1/2" Stud
- Hot Tin Dipped

- 250 kcmil
- 300 kcmil

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Certification - UL Listed Direct	No
Burial	
Buy America(n) Qualified	Contact Manufacturer
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - Copper Solid Size Range	4 AWG - 300 KCMIL
Conductor - Copper Str Size Range	5 AWG - 300 kcmil
Conductor - Copper Str Size	• 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	58.9 mm
Dimension - Height inch	2.32 in
Package Weight	0.000 lb.
Dimension - Width mm	38 mm
Dimension - Width inch	1.50 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	48 mm
Dimension - Width fraction	1-1/2 in
Dimension - Bus Thickness inch	0.31 in
Dimension - Length Overall inch	1.88 in
Dimension - Stud Size inch	33/64

Force Related

Installation Torque	480 lb-in
Recommended in-lb	

General

Physical Attribute - Screw Type	Hexagonal Bolt
Plated	Y
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810042748
Material	Copper Alloy
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810042748
UPC 14 Digit GTIN	00781810042748

Logistics

Minimum Pack Quantity	24
-----------------------	----

Product Assets

[Catalog \[English\]](#)