



GBM26OSB, Mechanical Grounding Connector, Cable to Bar

By Burndy
Catalog # [GBM26OSB](#)



Mechanical Grounding Connector; Cable to Bar, up to 1/4" Thick Bar, 4 Sol-2/0 Str Copper Conductor

Features

- Mechanical Grounding Connector
- Accommodates Bar up to 1/4" Thick
- 4 Sol-2/0 Str Copper Conductor

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG
Conductor - Copper Solid Size Range	4 AWG-2/0 AWG
Conductor - Copper Str Size Range	4 AWG - 2/0 AWG

Conductor - Copper Str Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG
-----------------------------	---

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
UPC	781810045442
Material Type - Screw	DURIUM™ Silicon Bronze
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810045442
UPC 14 Digit GTIN	00781810045442

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)