



GBM26T8, Mechanical Grounding Connector, Cable to Bar

By Burndy
Catalog # [GBM26T8](#)



Mechanical Grounding Connector, Cable to 1/4" - 1" Thick Bar, 4 AWG (Sol)-2/0 AWG (Str), 3/8" Stud.

Features

- High copper alloy ground connector for joining a range of cable to 1/4" thick bar
- Type GBM clamps cable directly on bar surface
- One-wrench installation
- UL467 Listed, Suitable for Direct Burial in earth or concrete

Specifications

UL Listed	Yes
Standards - RoHS Compliance Status	EX
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor - Copper Solid Size Range	#4 AWG-2/0 AWG
-------------------------------------	----------------

Dimensions

Dimension - Width inch	1.34 in
Dimension - Width mm	34 mm
Dimension - Width fraction	1-1/3 in

Force Related

Installation Torque Recommended in-lb	240 lb-in
---------------------------------------	-----------

General

UPC	781810079324
-----	--------------

Logistics

Minimum Pack Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)