



BURNDY

[GBM26W, Mech Ground Conn, Cable to Bar, Tin Plated](#)

By Burndy

Catalog # [GBM26W](#)

Mechanical Grounding Connector, Cable to 1/4" Thick Bar, 4 AWG (Sol)-2/0 AWG (Str), 3/8" Stud. Hot Tin Dipped



Features

- High copper alloy ground connector for joining a range of cable to 1/4" thick bar
- Type GBM clamps cable directly on bar surface
- One-wrench installation
- UL467 Listed, Suitable for Direct Burial in earth or concrete

Specifications

Certification - ETL

No

Certification - UL Recognized

No

Standards - Industry Standards Met
UL467
Standards - RoHS Compliance Status
EX
Certification - cULus
No
Certification - UL Listed Direct Burial
Yes
Buy America(n) Qualified
Contact Manufacturer
Industry Standard(s)
UL467
UL Listed
Yes
Certification - CSA Approved
No

Conductor

Conductor - Copper Solid Size Range
#4 AWG-2/0 AWG
Conductor - Copper Str Size Range
4 AWG - 2/0 AWG
Conductor - Copper Str Size

- 4 AWG
- 3 AWG
- 2 AWG
- 1 AWG
- 1/0
- 2/0 AWG

Dimensions

Package Height
0.000 in
Dimension - Height mm
37.8 mm
Dimension - Height inch
1.49 in
Package Weight
0.000 lb.
Dimension - Width mm
34 mm
Dimension - Width inch
1.34 in
Package Length
0.000 in
Package Width
0.000 in
Dimension - L Length Overall mm
24 mm
Dimension - Width fraction
1-1/3 in
Dimension - Length Overall inch
0.94 in

Force Related

Installation Torque Recommended in-lb
240 lb-in

General

Physical Attribute - Screw Type
Hexagonal Bolt
Plated
Y
UPC
781810117330
Material Type - Screw
DURIUM™ Silicon Bronze
Material
Copper Alloy
Plating Type
Tin - Hot Dipped
UPC 12 Digit
781810117330
UPC 14 Digit GTIN

00781810117330

Logistics

Minimum Pack Quantity

1

Pallet Quantity

1

Carton Quantity

1

Product Assets

[Catalog \(English\)](#)



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved

BRDY-GBM26W-SPEC-EN | REV 5/2026