



GBM29CG14, Mechanical Grounding Connector, Cable to Bar

By Burndy
Catalog # [GBM29CG14](#)



Mechanical Ground Connector

Features

- High copper alloy ground connector for joining a range of cable to 1/4" thick bar
- Type GBM clamps cable directly on bar surface
- One-wrench installation
- UL467 Listed, Suitable for Direct Burial in earth or concrete

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Plated	N
UPC	621945229457
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	621945229457
UPC 14 Digit GTIN	00621945229457

Logistics

Pallet Quantity	1
Carton Quantity	75

Product Assets

[Catalog \[English\]](#)