



GC2626G1T4, Mech Ground, Two Cables to Bar

By Burndy
Catalog # [GC2626G1T4](#)



Mechanical Grounding Connector, 2 Cables to Bar, 1/4" to 1/2"
Bar, 4 Sol - 2/0 Str

Features

- Mechanical Grounding Connector
- 2 Cables to Bar
- Accommodates 1/4"-1/2" Bar
- 4 Sol-2/0 Str Conductor

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.

Dimension - Width mm	42 mm
Dimension - Width inch	1.66 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	38 mm
Dimension - Width fraction	1-2/3 in
Dimension - Hole Size inch	0.44 in
Dimension - Length Overall inch	1.50 in

General

Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
UPC	781810106419
Material Type - Screw	DURIUM™ Silicon Bronze
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810106419
UPC 14 Digit GTIN	00781810106419

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)