



GC2626T4, Mechanical Grounding Connector, Two Cables to Bar

By Burndy
Catalog # [GC2626T4](#)

Mechanical Grounding Connector, 2 Cables to 1/4" - 1/2" Thick Bar, 4 AWG (Sol)-2/0 AWG (Str),



Features

- Mechanical Grounding Connector
- 2 Cables to 1/4"-1/2" Thick Bar
- 4 AWG (Sol)-2/0 AWG (Str)

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG
Conductor - Copper Solid Size Range	4 AWG-2/0 AWG
Conductor - Copper Str Size Range	4 AWG - 2/0 AWG
Conductor - Copper Str Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	44.2 mm
Dimension - Height inch	1.74 in
Package Weight	0.000 lb.
Dimension - Width mm	40 mm
Dimension - Width inch	1.57 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	25 mm
Dimension - Length Overall inch	1.00 in

Force Related

Installation Torque	240 lb-in
Recommended in-lb	

General

Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
UPC	781810231685
Material Type - Screw	DURIUM™ Silicon Bronze
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810231685
UPC 14 Digit GTIN	00781810231685

Logistics

Minimum Pack Quantity	35
Pallet Quantity	2200
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)