



GC2626W, Mech Ground, Two Cables to Bar, Tin Plated

By Burndy
Catalog # [GC2626W](#)



Mechanical Grounding Connector, 2 Cables to 1/4" Thick Bar; Hot Tin Dipped

Features

- Mechanical Grounding Connector
- 2 Cables to 1/4" Thick Bar
- 4 AWG Sol-2/0 AWG Str
- Hot Tin Dipped

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG
Conductor - Copper Solid Size Range	4 AWG-2/0 AWG
Conductor - Copper Str Size Range	4 AWG - 2/0 AWG
Conductor - Copper Str Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0

- 2/0 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	44.2 mm
Dimension - Height inch	1.74 in
Package Weight	0.000 lb.
Dimension - Width mm	40 mm
Dimension - Width inch	1.57 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	25 mm
Dimension - Length Overall inch	1.00 in

Force Related

Installation Torque	240 lb-in
Recommended in-lb	

General

Physical Attribute - Screw Type	Hexagonal Bolt
Plated	Y
UPC	781810079393
Material Type - Screw	DURIUM™ Silicon Bronze
Material	Copper
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810079393
UPC 14 Digit GTIN	00781810079393

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)