

GC30G3, Mechanical Ground Connector

By Burndy
Catalog # [GC30G3](#)

Ground Connector, Copper Cable: #4 AWG - 300 kcmil



Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size Range	#4 AWG - 300 KCMIL
Conductor - Copper Str Size Range	4 AWG - 300 kcmil
Conductor - Copper Str Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil

Dimensions

Package Height	0.000 in
Dimension - Height mm	83.1 mm
Dimension - Height inch	3.27 in
Package Weight	0.000 lb.
Dimension - Width mm	48 mm
Dimension - Width inch	1.88 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	61 mm
Dimension - Width fraction	1-7/8 in
Dimension - Length Overall inch	2.41 in

General

Physical Attribute - Screw Type Plated	Oval Shank Bolt N
UPC	781810117460
Material Type - Screw Material	DURIUM™ Silicon Bronze Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810117460
UPC 14 Digit GTIN	00781810117460

Logistics

Pallet Quantity	216
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)