



GC3939, Mechanical Grounding Connector, Two Cables to Bar

By Burndy
Catalog # [GC3939](#)



Mechanical Grounding Connector, 2 Copper Cables to 1/4" Thick Bar, 550 kcmil - 750 kcmil, 5/8" Stud

Features

- High copper alloy ground connector for joining a wide range of 2 parallel cables to 1/2" thick bar
- Type GC separates cable from bar
- Type GCM clamps cable direct to bar surface
- One wrench installation
- UL467 Listed
- Suitable for Direct Burial in earth or concrete

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size Range	550 KCMIL - 750 KCMIL
Conductor - Copper Str Size Range	550 kcmil - 750 kcmil
Conductor - Copper Str Size	• 550 kcmil • 600 kcmil • 700 kcmil • 750 kcmil

Dimensions

Dimension - Pad Width inch	1.75 in
Package Height	0.000 in
Dimension - Height mm	84 mm
Length	2.25 in

Dimension - Height inch	3.31 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.56 in
Package Width	0.000 in
Dimension - L Length Overall mm	57 mm
Dimension - B Length inch	3.63 in
Height	3.31 in
Width	3.63 in
Dimension - Length Side A inch	2.25 in
Dimension - Length Side B inch	3.06 in
Dimension - D inch	3.31 in
Dimension - Length Overall inch	2.25 in
Dimensions	2.25 in x 3.63 in x 3.31 in

Force Related

Installation Torque	660 lb-in
Recommended in-lb	

General

Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
UPC	781810001660
Material Type - Screw	DURIUM™ Silicon Bronze
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810001660
UPC 14 Digit GTIN	00781810001660

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)