



GCG63T13G1, Bronze Ground Conn for Static Ground Application

By Burndy
Catalog # [GCB63T13G1](#)

Bronze Ground Connector, 2.28 in L, .63 dia Ball, 1/2" Stud, silicon bronze hardware

Features

- Includes 1/2" Silicon Bronze Split Washer, 1/2"-13 Silicon Bronze Hex Head Nut

Application

For use on rail cars, chemical trucks, hazardous waste tankers or a petroleum vehicle to allow for static grounding protection,

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
UL Listed	No
Certification - CSA Approved	No

Dimensions



Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Sub Brand	MECHANICAL CONNECTOR
UPC	781810126578
Type	Ground Connector
Material	Bronze
UPC 12 Digit	781810126578
UPC 14 Digit GTIN	00781810126578

Logistics

Minimum Pack Quantity	1
Pallet Quantity	11100
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)