



GCL30, Mechanical Grounding Connector, Two Cables to Bar

By Burndy

Catalog # [GCL30](#)

Cast Copper Alloy Ground Clamp, 2 Cables to Bar, Bar up to 1/4" Thick,
#4 AWG-300 kcmil, 1/2" Stud, Silicon Bronze Hardware



Features

- High copper alloy ground connector for joining a range of two parallel cables to 1/4" thick bar
- Type GC Separates cable from bar
- One-wrench installation
- UL467 Listed

Application


For Two Copper Cables To Bar And Direct Burial In Concrete Or Ground

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	Yes
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 4 Str • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil
Conductor - Copper Solid Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - Copper Solid Size Range	4 AWG - 300 KCMIL
Conductor - Copper Str Size Range	4 AWG - 300 kcmil



Dimensions

Package Height	0.000 in
Dimension - Height mm	50.8 mm
Dimension - Height inch	2.00 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	56 mm
Dimension - Stud Size inch	33/64
Dimension - Width mm	38 mm
Dimension - Width inch	1.50 in
Dimension - Bus Thickness inch	0.25 in
Dimension - Length Overall inch	2.21 in

Force Related

Installation Torque Recommended in-lb	480 lb-in
---------------------------------------	-----------

General

Product Family	Grounding and Bonding Connectors>Copper Mechanical Grounding Connectors>Cable(s) to Bar/Flat
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	No
Sub Brand	MECHANICAL CONNECTOR
Product Type	Mechanical
UPC	781810079478
Type	GC
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810079478
UPC 14 Digit GTIN	00781810079478

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4536
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)