



GCL30GS, Mech Ground, Two Cables to Bar, Galvanized Steel

By Burndy
Catalog # [GCL30GS](#)

Mechanical Grounding Connector, 2 Copper Cables to 1/4" Thick Bar, #4 AWG - 300 kcmil, 1/2" Stud, Galvanized Steel Hardware



Features

- Mechanical Grounding Connector
- 2 Copper Cables to 1/4" Thick Bar
- #4 AWG-300 kcmil
- 1/2" Stud
- Galvanized Hardware

- 250 kcmil
- 300 kcmil

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - Copper Solid Size Range	4 AWG - 300 KCMIL
Conductor - Copper Str Size Range	5 AWG - 300 kcmil
Conductor - Copper Str Size	• 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	50.8 mm
Dimension - Height inch	2.00 in
Package Weight	0.000 lb.
Dimension - Width mm	38 mm
Dimension - Width inch	1.50 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	56 mm
Dimension - Bus Thickness inch	0.25 in
Dimension - Length Overall inch	2.21 in
Dimension - Stud Size inch	33/64

Force Related

Installation Torque	480 lb-in
Recommended in-lb	

General

Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Material - Hardware	Galvanized Steel
UPC	781810100950
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810100950
UPC 14 Digit GTIN	00781810100950

Logistics

Minimum Pack Quantity	20
Pallet Quantity	432
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)