



GCL30P2W, Mechanical Grounding Connector

By Burndy
Catalog # [GCL30P2W](#)

Mechanical Ground Connector, #4 Solid - 300 kcmil Copper, Hot Dip Tin Plate



Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - Copper Solid Size Range	4 AWG-4/0 AWG
Conductor - Copper Str Size Range	5 AWG - 300 kcmil
Conductor - Copper Str Size	• 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Dimension - Width mm	38 mm
Dimension - Width inch	1.50 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	53 mm
Dimension - Bus Thickness inch	.25 in
Dimension - Length Overall inch	2.07 in

Force Related

Installation Torque	480 LBS/in
Recommended in-lb	

General

Plated	Y
Material - Hardware	Copper Alloy
UPC	781810100974
Material	Copper Alloy
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810100974
UPC 14 Digit GTIN	00781810100974

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)