



GCL30T4, Mechanical Ground Connector, Cable to Bar

By Burndy
Catalog # [GCL30T4](#)

Mechanical Grounding Connector, 2 Copper Cables to 1/4" - 1/2" Thick Bar, #4 AWG - 300 kcmil, 1/2" Stud

Features

- Mechanical Grounding Connector
- 2 Copper Cables to 1/4"-1/2" Thick Bar
- 4 AWG-300 kcmil
- 1/2" Stud

Specifications

Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor - Copper Solid Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - Copper Solid Size Range	4 AWG - 300 KCMIL
Conductor - Copper Str Size Range	5 AWG - 300 kcmil
Conductor - Copper Str Size	• 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil



Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Dimension - Width mm	38 mm
Dimension - Width inch	1.50 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	56 mm
Dimension - Bus Thickness inch	0.25 in
Dimension - Length Overall inch	2.21 in
Dimension - Stud Size inch	33/64

Force Related

Installation Torque	480 lb-in
Recommended in-lb	

General

Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810122303
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810122303
UPC 14 Digit GTIN	00781810122303

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)