



GCL30W, Mech Ground, 2 Copper Cables to Bar, Tin Plated

By Burndy
Catalog # [GCL30W](#)

Mechanical Grounding Connector, 2 Copper Cables to 1/4" Thick Bar, #4 AWG - 300 kcmil, 1/2" Stud



Features

- Mechanical Grounding Connector
- 2 Copper Cables to 1/4" Thick Bar
- #4 AWG-300 kcmil
- 1/2" Stud
- Hot Tin Dipped

- 4/0 AWG
- 250 kcmil
- 300 kcmil

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
Certification - UL Listed Direct	Yes
Burial	
Buy America(n) Qualified	Contact Manufacturer
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - Copper Solid Size Range	4 AWG - 300 KCMIL
Conductor - Copper Str Size Range	5 AWG - 300 kcmil
Conductor - Copper Str Size	• 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	50.8 mm
Dimension - Height inch	2.00 in
Package Weight	0.000 lb.
Dimension - Width mm	38 mm
Dimension - Width inch	1.50 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	56 mm
Dimension - Bus Thickness inch	0.25 in
Dimension - Length Overall inch	2.21 in
Dimension - Stud Size inch	33/64

Force Related

Installation Torque	480 lb-in
Recommended in-lb	

General

Physical Attribute - Screw Type	Hexagonal Bolt
Plated	Y
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810042755
Material	Copper Alloy
UPC 12 Digit	781810042755
UPC 14 Digit GTIN	00781810042755

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)