



GCM28CG3, Mechanical Grounding Connector, 2 Cables to Bar

By Burndy
Catalog # [GCM28CG3](#)

Mechanical Grounding Connector, #1 AWG (Sol)-4/O AWG (Str),
1/4" Stud, Electro-Tinned



Features

- High copper alloy ground connector for joining a wide range of 2 parallel cables to 1/2" thick bar
- Type GC separates cable from bar
- Type GCM clamps cable direct to bar surface
- One wrench installation
- UL467 Listed
- Suitable for Direct Burial in earth or concrete

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 1 AWG • 1/O AWG • 2/O AWG • 3/O AWG • 4/O AWG
Conductor - Copper Solid Size Range	#1 AWG-4/O AWG
Conductor - Copper Str Size Range	1 AWG - 4/O AWG
Conductor - Copper Str Size	• 1 AWG • 1/O • 2/O AWG • 3/O AWG

- 4/O AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Dimension - Width mm	51 mm
Dimension - Width inch	2.00 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	41 mm
Dimension - Width fraction	2 in
Dimension - Length Overall inch	1.62 in

Force Related

Installation Torque	45 lb-in
Recommended in-lb	

General

Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
UPC	781810421932
Material Type - Screw	DURIUM™ Silicon Bronze
Material	Copper Alloy
Plating Type	Electro-Tinned
UPC 12 Digit	781810421932
UPC 14 Digit GTIN	00781810421932

Logistics

Minimum Pack Quantity	20
Pallet Quantity	1800
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)