



GD1526, Mech Ground, 2 Cables to Rod or Pipe

By Burndy
Catalog # [GD1526](#)



Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 4 AWG (Sol.) - 2/0 AWG (Str.), 1-1/8" to 1-1/4" Rod, 1" Pipe

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Application

For Joining A Range Of Two Parallel Cables To Rod Or Tube, Grounding Fence Posts, Direct Burial Applications In Earth Or Concrete

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	EX
Status	
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Rod Size Range	1 1/4 in
Conductor - Copper Str Size	• 4 • 3 • 2 • 1 • 1/0 • 2/0
Conductor - Rod Size	1 1/4 in
Conductor - Copper Solid Size	• 4 • 3 • 2 • 1 • 1/0 • 2/0
Conductor - Copper Solid Size Range	4-2/0
Conductor - Copper Str Size Range	4 AWG - 2/0 AWG
Conductor - Copper Str Size B Range	1

Conductor - Copper Tube Std Size Range	1-1/8-1-1/4
Conductor - Copper Tube Std Size	• 1-1/8 • 1-1/4

Dimensions

Package Height	0.000 in
Dimension - Height mm	85.9 mm
Dimension - Height inch	3.38 in
Dimension - Height fraction	3-3/8 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Width fraction	2-5/8 in
Dimension - Width mm	67 mm
Dimension - Width inch	2.63 in
Dimension - B Length inch	1.13 in

Force Related

Installation Torque Recommended in-lb	240 LBS/in
---------------------------------------	------------

General

Product Family	Grounding and Bonding Connectors>Copper Mechanical Grounding Connectors>Cable(s) to Ground Rod/Pipe/Tube (GAR/GD/GK)>Two Conductor (GD)
Material Type - Screw Plated	DURIUM™ Silicon Bronze No
Sub Brand	MECHANICAL CONNECTOR
Product Type	Mechanical
UPC	781810260258
Type	GD
U Bolt Type	244
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810260258
UPC 14 Digit GTIN	00781810260258

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2880
Carton Quantity	12



A Hubbell brand