

GD1529, Mech Ground Conn, 2 Cables to Rod or Pipe

By Burndy
Catalog # [GD1529](#)

Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 2/0 AWG (Sol.) - 200 kcmil, 1-1/8" to 1-1/4" Rod, 1" Pipe



Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 2/0 • 3/0 • 4/0
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Rod Size Range	1 1/4 in
Conductor - Copper Str Size Range	2/0 AWG - 250 kcmil
Conductor - Copper Str Size	• 2/0 • 3/0 • 4/0 • 250
Conductor - Rod Size	1 1/4 in
Conductor - Copper Str Size Range	1
Conductor - Copper Tube Std Size Range	1-1/8-1-1/4

Conductor - Copper Tube Std Size	• 1-1/8 • 1-1/4
----------------------------------	---

Dimensions

Package Height	0.000 in
Dimension - Height mm	85.9 mm
Dimension - Height inch	3.38 in
Dimension - Height fraction	3-3/8 in
Package Weight	0.000 lb.
Dimension - Width mm	67 mm
Dimension - Width inch	2.63 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.13 in
Dimension - Width fraction	2-5/8 in

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	

General

Plated	N
UPC	781810260265
Material Type - Screw	DURIUM™ Silicon Bronze
U Bolt Type	244
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810260265
UPC 14 Digit GTIN	00781810260265

Logistics

Minimum Pack Quantity	4
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)