

GD1629CG1, Mech Ground Conn, 2 Cables to Rod or Pipe

By Burndy
Catalog # [GD1629CG1](#)



Mechanical Ground Clamp, 2 Cables to Rod or Pipe, 1-1/4" IPS, 3/8"-1-1/4" Rod, 2/0 Solid AWG Min, 250 kcmil Cu Max

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 2/0 • 3/0 • 4/0
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Copper Str Size Range	2/0 AWG - 250 kcmil
Conductor - Copper Str Size	• 2/0 • 3/0 • 4/0 • 250
Conductor - Copper Str Size B Range	1.25

Dimensions

Package Height	0.000 in
Dimension - Height mm	104.6 mm
Dimension - Height inch	4.12 in
Package Weight	0.000 lb.
Dimension - Width mm	83 mm
Dimension - Width inch	3.25 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.25 in
Dimension - Width fraction	3-1/4 in

Force Related

Installation Torque	360 LBS/in
Recommended in-lb	

General

Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
UPC	621945138995
Material Type - Screw	Steel - Galvanized
Material	Copper Alloy, Cast
Plating Type	Tin - Electro Plated
UPC 12 Digit	621945138995
UPC 14 Digit GTIN	00621945138995

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)