



GD1726TN, Mech Ground Conn, 2 Cables to Rod/Pipe, Tin Plated

By Burndy
Catalog # [GD1726TN](#)



Mechanical Ground Clamp, Accommodates: 1-1/2" IPS, 1-4/8" - 1-7/8" Copper Rod; #4 Sol-2/0 Str Conductor; Tin Plated, Direct Burial

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 4 • 3 • 2 • 1 • 1/0 • 2/0
Conductor - Copper Solid Size Range	4-2/0
Conductor - Copper Str Size	4 AWG - 2/0 AWG
Conductor - Copper Str Size Range	• 4 • 3 • 2 • 1 • 1/0 • 2/0
Conductor - Copper Str Size B Range	1.5

Conductor - Copper Tube Std Size Range	1-5/8-1-7/8
Conductor - Copper Tube Std Size	• 1-5/8 • 1-3/4 • 1-7/8

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Dimension - Width mm	83 mm
Dimension - Width inch	3.25 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.31 in
Dimension - Width fraction	3-1/4 in

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	

General

Plated	Y
UPC	781810343456
Material Type - Screw	DURIUM™ Silicon Bronze
U Bolt Type	268
Material	Copper Alloy
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810343456
UPC 14 Digit GTIN	00781810343456

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)