

GD1729TN, Mech Ground Conn, 2 Cables to Rod/Pipe, Tin Plated

By Burndy
Catalog # [GD1729TN](#)



Mechanical Ground Connector, Accommodates 2/0 AWG Sol-250 kcmil; 1-1/2" Pipe, 1-4/8" to 1-7/8" Rod, Tin Plated, Supplied with #6 silicon bronze hardware

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 2/0 • 3/0 • 4/0
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Copper Str Size	2/0 AWG - 250 kcmil
Conductor - Copper Str Size Range	• 2/0 • 3/0 • 4/0 • 250
Conductor - Copper Str Size B Range	1.5
Conductor - Copper Tube Std Size Range	1-5/8-1-7/8

Conductor - Copper Tube Std Size	• 1-5/8 • 1-3/4 • 1-7/8
----------------------------------	---

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Dimension - Width mm	83 mm
Dimension - Width inch	3.25 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.31 in
Dimension - Width fraction	3-1/4 in

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	

General

Plated	Y
UPC	781810416785
Material Type - Screw	DURIUM™ Silicon Bronze
U Bolt Type	268
Material	Copper Alloy, Cast
Plating Type	Tin Plated
UPC 12 Digit	781810416785
UPC 14 Digit GTIN	00781810416785

Logistics

Minimum Pack Quantity	12
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)