



GD1829CG1, Mech Ground Conn, 2 Cables to Rod or Pipe

By Burndy
Catalog # [GD1829CG1](#)



Mechanical Ground Clamp, 2" IPS Aluminum Pipe - 250 kcmil to 2/0 Solid Cast Copper Alloy

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 2/0 • 3/0 • 4/0
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Copper Str Size Range	2/0 AWG - 250 kcmil
Conductor - Copper Str Size	• 2/0 • 3/0 • 4/0 • 250

Conductor - Copper Str Size B Range 2

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Height inch	5 in
Package Weight	0.000 lb.
Dimension - Width mm	102 mm
Dimension - Width inch	4 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.25 in
Dimension - Width fraction	4 in

General

Plated	N
UPC	621945157439
Material Type - Screw	Steel - Galvanized
Material	Copper Alloy, Cast
Plating Type	Brite Dip
UPC 12 Digit	621945157439
UPC 14 Digit GTIN	00621945157439

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)