



GD1829W, Mech Ground Conn, 2 Cables to Rod/Pipe, Tin Plated

By Burndy
Catalog # [GD1829W](#)



Mechanical Ground Clamp, Accommodates: 2 IPS 2" OD, Tube:
2/0 Sol (.36 dia) - 250 kcmil (.575 dia) Copper

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 2/0 • 3/0 • 4/0
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Copper Str Size Range	2/0 AWG - 250 kcmil
Conductor - Copper Str Size	• 2/0 • 3/0 • 4/0 • 250
Conductor - Copper Str Size B Range	2
Conductor - Copper Tube Std Size Range	2

Conductor - Copper Tube Std Size 2

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Dimension - Width mm	94 mm
Dimension - Width inch	3.69 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.31 in
Dimension - Width fraction	3-2/3 in

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	

General

Plated	Y
UPC	781810099926
Material Type - Screw	DURIUM™ Silicon Bronze
U Bolt Type	257
Material	Copper Alloy
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810099926
UPC 14 Digit GTIN	00781810099926

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)