



# GD194C, Mech Ground Conn, 2 Cables to Rod or Pipe

By Burndy  
Catalog # [GD194C](#)



Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 8 AWG (Sol.) - 4 AWG (Str.), 2-1/2" Rod, 2-1/2"- to 2-7/8" Pipe

### Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

### Specifications

|                                         |                      |
|-----------------------------------------|----------------------|
| Certification - ETL                     | No                   |
| Certification - UL Recognized           | No                   |
| Standards - Industry Standards Met      | UL467                |
| Standards - RoHS Compliance Status      | EX                   |
| Certification - cULus                   | No                   |
| Certification - UL Listed Direct Burial | Yes                  |
| Buy America(n) Qualified                | Contact Manufacturer |
| Industry Standard(s)                    | UL467                |
| UL Listed                               | Yes                  |
| Certification - CSA Approved            | No                   |

### Conductor

|                                     |                                                                                                     |
|-------------------------------------|-----------------------------------------------------------------------------------------------------|
| Conductor - Copper Solid Size       | <ul style="list-style-type: none"><li>• 8</li><li>• 7</li><li>• 6</li><li>• 5</li><li>• 4</li></ul> |
| Conductor - Copper Solid Size Range | 8-4                                                                                                 |
| Conductor - Rod Size Range          | 2 1/2 in                                                                                            |
| Conductor - Copper Str Size Range   | 8 AWG - 4 AWG                                                                                       |
| Conductor - Copper Str Size         | <ul style="list-style-type: none"><li>• 8</li><li>• 7</li><li>• 6</li><li>• 5</li><li>• 4</li></ul> |
| Conductor - Rod Size                | 2 1/2 in                                                                                            |
| Conductor - Copper Str Size B Range | 2.5                                                                                                 |

|                                        |       |
|----------------------------------------|-------|
| Conductor - Copper Tube Std Size Range | 2-1/2 |
| Conductor - Copper Tube Std Size       | 2-1/2 |

### Dimensions

|                             |           |
|-----------------------------|-----------|
| Package Height              | 0.000 in  |
| Dimension - Height mm       | 127 mm    |
| Dimension - Height inch     | 5.00 in   |
| Dimension - Height fraction | 5 in      |
| Package Weight              | 0.000 lb. |
| Dimension - Width mm        | 106 mm    |
| Dimension - Width inch      | 4.19 in   |
| Package Length              | 0.000 in  |
| Package Width               | 0.000 in  |
| Dimension - B Length inch   | 1.38 in   |
| Dimension - Width fraction  | 4-1/4 in  |

### Force Related

|                                       |            |
|---------------------------------------|------------|
| Installation Torque Recommended in-lb | 240 LBS/in |
|---------------------------------------|------------|

### General

|                       |                        |
|-----------------------|------------------------|
| Plated                | N                      |
| UPC                   | 781810260357           |
| Material Type - Screw | DURIUM™ Silicon Bronze |
| U Bolt Type           | 266                    |
| Material              | Copper Alloy, Cast     |
| Plating Type          | Unplated               |
| UPC 12 Digit          | 781810260357           |
| UPC 14 Digit GTIN     | 00781810260357         |

### Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 6   |
| Pallet Quantity       | 216 |
| Carton Quantity       | 6   |

### Product Assets

[Catalog \[English\]](#)