



GD2034, Mech Ground Conn, 2 Cables to Rod or Pipe

By Burndy
Catalog # [GD2034](#)



Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 300 - 500 kcmil, 3" Rod, 3" to 3-1/2" Pipe

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Rod Size Range	3 in
Conductor - Copper Str Size Range	300 kcmil - 500 kcmil
Conductor - Copper Str Size	• 300 • 350 • 400 • 450 • 500
Conductor - Rod Size	3 in
Conductor - Copper Str Size B Range	3
Conductor - Copper Tube Std Size Range	3
Conductor - Copper Tube Std Size	3

Dimensions

Package Height	0.000 in
Dimension - Height mm	162.1 mm
Dimension - Height inch	6.38 in
Dimension - Height fraction	6-3/8 in
Package Weight	0.000 lb.
Dimension - Width mm	135 mm
Dimension - Width inch	5.31 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.56 in
Dimension - Width fraction	5-1/4 in

Force Related

Installation Torque	480 LBS/in
Recommended in-lb	

General

Plated	N
UPC	781810260401
Material Type - Screw	DURIUM™ Silicon Bronze
U Bolt Type	282
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810260401
UPC 14 Digit GTIN	00781810260401

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)