

GD2126, Mech Ground Conn, 2 Cables to Rod or Pipe

By Burndy
Catalog # [GD2126](#)

Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 4 AWG (Sol.) - 2/0 AWG (Str.), 3-1/2" to 4" Rod, 3-1/2" Pipe

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Application

For Joining A Range Of Two Parallel Copper Cables To Rod Or Pipe And Burial In Ground Or Concrete

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 4 • 3 • 2 • 1 • 1/0 • 2/0
Conductor - Copper Solid Size	• 4 • 3 • 2 • 1 • 1/0 • 2/0
Conductor - Copper Solid Size Range	4-2/0
Conductor - Copper Str Size Range	4 AWG - 2/0 AWG



Conductor - Copper Str Size B Range	3.5
Conductor - Copper Tube Std Size Range	3-1/2
Conductor - Copper Tube Std Size	3-1/2

Dimensions

Package Height	0.000 in
Dimension - Height mm	158.8 mm
Dimension - Height inch	6.25 in
Dimension - Height fraction	6-1/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Width fraction	5-3/8 in
Dimension - Width mm	135 mm
Dimension - Width inch	5.31 in
Dimension - B Length inch	1.50 in

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	

General

Material Type - Screw Plated	DURIUM™ Silicon Bronze N
Sub Brand	MECHANICAL CONNECTOR
UPC	781810260425
Type	GD
U Bolt Type	264
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810260425
UPC 14 Digit GTIN	00781810260425

Logistics

Pallet Quantity	120
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)